

CANALKLER 250 S ASSEMBLY



CONSTRUCTION & INFRASTRUCTURE

Drain and sewer cleaning



APPLICATIONS

Sewer jetting and heavy duty, high pressure water cleaning.

ADVANTAGES

- ¹ Very low sliding resistance which allows: higher cleaning efficiency, reduction of cleaning time and therefore, reduction of fuel consumption.
- ¹ Longer lifespan thanks to the special cover compound with higher abrasion resistance.
- ¹ Better flexibility, even at low temperatures.
- ¹ Easy to handle and user friendly.
- ¹ Deformation resistance.
- ¹ Extra high strength and security due to aramide reinforcement.

TECHNICAL DESCRIPTION

Inner tube: SBR, black, smooth.

Reinforcement: aramide textile, braided.

Cover: SBR/NR, black, smooth. Very low sliding resistance.

Temperature range: -30 °C to +80 °C.

COUPLINGS/FITTINGS


All hoses are assembled with BSP female/BSP male.

All assembled hoses are pressure tested at 375bar and have an unique hose number.

COMPLEMENTARY INFORMATION

Delivered with test certificate on each factory assembled hose.

Embossed branding



CONSTRUCTION & INFRASTRUCTURE			CANALKLER 250 S ASSEMBLY						
ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (.) or min. order m
13.0 ±0.5	6.3 ±0.5	25.6	250	625	70	0.45	40	5014178	1
13.0 ±0.5	6.3 ±0.5	25.6	250	625	70	0.45	60	5014179	1
13.0 ±0.5	6.3 ±0.5	25.6	250	625	70	0.45	80	5014180	1
13.0 ±0.5	6.3 ±0.5	25.6	250	625	70	0.45	100	5014916	1
13.0 ±0.5	6.3 ±0.5	25.6	250	625	70	0.45	120	5014005	1
19.0 ±0.6	6.3 ±0.5	31.6	250	625	90	0.61	40	5014181	1
19.0 ±0.6	6.3 ±0.5	31.6	250	625	90	0.61	80	5014182	1
19.0 ±0.6	6.3 ±0.5	31.6	250	625	90	0.61	100	5014459	1
19.0 ±0.6	6.3 ±0.5	31.6	250	625	90	0.61	120	5014006	1
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	40	5014183	1
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	50	5014874	1
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	80	5014184	1
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	100	5014238	1
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	120	5014007	1
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	150	5014461	1
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	160	5014185	1
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	180	5014186	1
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	200	5014520	1
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	240	5014733	1
32.0 ±1.0	7.8 ±0.6	47.6	250	625	130	1.12	40	5014187	1
32.0 ±1.0	7.8 ±0.6	47.6	250	625	130	1.12	80	5014188	1
32.0 ±1.0	7.8 ±0.6	47.6	250	625	130	1.12	120	5014008	1
32.0 ±1.0	7.8 ±0.6	47.6	250	625	130	1.12	150	5014466	1
32.0 ±1.0	7.8 ±0.6	47.6	250	625	130	1.12	160	5014189	1
32.0 ±1.0	7.8 ±0.6	47.6	250	625	130	1.12	180	5014190	1
32.0 ±1.0	7.8 ±0.6	47.6	250	625	130	1.12	200	5014655	1
38.0 ±1.0	8 ±0.8	54.0	250	500	155	1.35	120	5014009	360
Tolerance on length: ±1% (ISO 1307 Standard).									

Digital version



WWW.TRELLEBORG.COM/FLUIDHANDLING